

Eco-Surge 8-Outlet Surge Protector, 8-ft. Cord, 2160 Joules, Diagnostic LEDs

MODEL NUMBER: TLP808NETG



Description

Tripp Lite's TLP808NETG offers reliable, green surge technology that protects your computer and peripherals, the environment and your wallet. The TLP808NETG offers a unique Netbook switch that allows users to select wattage, so these are the only green surge suppressors compatible with all PCs, Notebooks and Netbooks. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. TLP808NETG offers 8 total outlets, 1-line tel/network data line to protect surges from damaging your modem/fax/100Bt equipment, 8 foot cord with space-saving angled plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 2160 joules shields equipment from surges and line noise. Integrated child-safety outlet covers safely seal off unused outlets. Attractive cool gray suppressor housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$150,000 connected equipment insurance (U.S., Canada, and Puerto Rico only). PLUG/OUTLETS: Input: NEMA5-15P/Output: 8 NEMA5-15R/8 ft. AC line cord ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle) FORMAT: Corded multi-outlet strip with transformer spaced outlets SUPPRESSION AC: 150V RMS Clamping/2160 joules

Features

- Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals
- Allows users to switch between green (auto) power save mode and standard (manual) surge protection mode
- 8 total AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- "Master" outlet controls power flow for 1 primary device and up to 5 peripheral devices
- Five "Power Save" outlets cut AC power when not in use--perfect for non-essential peripherals like monitors, printers, scanners, speakers, lamps, etc.
- Two "Always-On" outlets provide continuous power for interminable devices such as modems, routers, external hard drives, cordless phones and fax machines
- 1-line tel/network data line protection to prevent surges from damaging your modem/fax/100Bt equipment
- User-selectable wattage switch accommodates PCs, Netbooks and other Internet research tools
- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- Long 8 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection

Highlights

- 8 outlets / 8-ft. cord
- 2160 joule rating
- Auto/Manual switch offers green energy savings or standard protection
- Unique Netbook switch allows user to select wattage
- 1-line tel/network protection
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection.

Package Includes

- TLP808NETG Eco Energy-Saving Surge Suppressor
- 6-ft. tel/network cable
- Instruction manual with warranty information



- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive gray suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Output Watt Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 3 large transformer plug accessories without covering remaining outlets
Outlet Details	Includes built-in sliding safety covers
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	8
Input Cord Length (m)	2.4
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160



AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330 L-G, 400 L-N, 400 N-G
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.05 x 8.66 x 11.4
Shipping Dimensions (hwd / cm)	5.21 x 22.00 x 28.99
Shipping Weight (lbs.)	2.05
Shipping Weight (kg)	0.93
Unit Dimensions (hwd / in.)	1.51 x 4.86 x 9.55
Unit Dimensions (hwd / cm)	3.84 x 12.34 x 24.26
Unit Weight (lbs.)	1.87
Unit Weight (kg)	0.85
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal slots = 75mm; Distance between vertical slots = 41.6mm
SPECIAL FEATURES	
Green Energy-Saving Features	Power saving auto-shutoff ECO outlets
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.