

7-Port Rugged Industrial USB 2.0 Hi-Speed Hub w 15KV ESD Immunity and metal case, Mountable

MODEL NUMBER: **U223-007-IND**



Description

Tripp Lite's U223-007-IND is a rugged, all metal constructed USB 7-Port hub for use in data centers, work areas, and Industrial applications. Can be mounted on a wall or din-rail with included mounting hardware. Supports Hi-Speed USB 2.0 transfer rates at 480mbps, but is also backward compatible to USB 1.1 (12mbps). Hub is bus-powered through the computer connection, or can self power with an external adapter (not included) or via the included 3-wire terminal block connector (9-36V).

Features

- Industrial-grade, rugged all metal 7-port USB hub
- Supports USB 1.1 and 2.0 transfer speeds (12 - 480mbps)
- Wall or Din Rail mountable - hardware included
- Bus Powered or optional 3-Wire DC Terminal Block
- Over-current detection and protection circuit design
- ESD protected to $\pm 15kV$
- Automatic link and speed detection
- Plug-and-Play; no software or drivers
- Compatible with all major operating systems

Specifications

OVERVIEW	
Chromebook Compatible	No
Over Current Protection	Yes

Highlights

- Industrial-grade, rugged metal enclosure
- ESD Protected to $\pm 15 kV$
- USB 2.0 Compliant - 480Mbps
- Compatible with all major operating systems

Applications

- Use in areas where hub needs to be securely fastened to a surface, such as din rail or wall
- Use in locations where environment is extreme or possible damage could occur

System Requirements

- Compatible with all major operating systems

Package Includes

- U223-007-IND Hub
- 6ft USB cable x 1
- 3-pin power terminal block
- DIN rail mounting hardware
- Wallmount hardware



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
USB Charging	No
PHYSICAL	
Unit Dimensions (hwd / in.)	1 x 2.5 x 5.6
Unit Dimensions (hwd / cm)	2.5 x 6.4 x 14.2
Material of Construction	Metal
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Relative Humidity	5 to 95% RH
Operating Temperature	0C to 60C (32F to 140F)
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	USB A (FEMALE) (X7)
Number of Connectors	8
Ports	7
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.