

USB 2.0 Hi-Speed to Serial atA (Sata) and IDE Adapter for 2.5in or 3.5in Hard Drives

MODEL NUMBER: **U238-000-1**



Description

Tripp Lite's USB 2.0 to SATA / IDE Adapter allows individual or simultaneous connection to either a Serial ATA or IDE drive (2.5" / 3.5" / 5.25"). You can also transfer data between a SATA and an IDE drive over the adapter. It provides a convenient, efficient way to format hard drives or transfer files without having to install them first. With the U238-000-1, any SATA or IDE drive can be conveniently turned into an external USB 2.0 storage drive. PC Clone EX Lite software is included to allow you to quickly backup and restore files. The backup button on the unit allows for quick backup of your files with the press of a button. PC Clone Ex Lite is compatible with Windows. The U238-000-1 is compatible with Windows, Mac, and Linux.

Features

- USB 2.0 and SATA 1.0a Compliant
- Operates with one IDE and one SATA drive simultaneously
- Supports Plug-n-Play
- USB Mass Storage Class Bulk-Only Transport specification
- 40-pin and 44-pin IDE connectors, and a 22-Pin SATA Data + Power connector
- Compatible with 2.5" / 3.5" / 5.25" SATA and IDE drives
- Includes PC Clone Ex Lite backup and restore software, and features a button for one touch backup
- Compatible with Windows, Mac, and Linux

Specifications

Highlights

- Easily transfer between SATA and IDE drives via USB
- Ideal for configuring hard drives without having to install them first
- USB 2.0 and SATA 1.0a compliant
- Compatible with 2.5" / 3.5" / 5.25" SATA and IDE drives
- Includes PC Clone Ex Lite backup and restore software
- Compatible with Windows, Mac, and Linux

Applications

- Formatting hard drives, file transfers, or external storage

System Requirements

- 2.5" / 3.5" / 5.25" SATA and/or IDE drive
- Computer with an available USB port
- PC Clone Ex Lite software compatible with Windows
- U238-000-1 compatible with Windows, Mac, and Linux

Package Includes

- USB 2.0 to SATA/IDE Combo Adapter
- USB 2.0 Cable - 5-Pin Mini B Male to A Male
- 4-Pin Molex Power Cable
- External Power Supply (Input: 100-240V, 50/60Hz, 0.8A Output: 12V, 2A)
- Backup Software CD
- Owner's Manual

OVERVIEW	
Chromebook Compatible	Yes
Model Type	Adapters



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	USB MINI-B 5-PIN (FEMALE)
Connector B	22 PIN SATA + POWER (FEMALE)
Connector C	40 POS. SOCKET (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.