

Universal Reversible USB 2.0 Hi-Speed Adapter (Reversible A to A M/F)

MODEL NUMBER: **UR024-000**



Highlights

- Universal / Reversible A-Male plugs in any direction
- Turns a standard USB cable into a Universal Cable
- USB2.0 Rated

Package Includes

- Universal Reversible USB 2.0 A-Male to A-Female Adapter

Description

Tripp Lite's UR024-000, USB Male to Female adapter, features a Universal / Reversible Male end which allows the adapter to be plugged in any direction on a computer's USB port. Add this adapter to a standard USB cable, and convert it to a Universal pluggable cable. USB2.0 rated for 480Mbps transfer rates. Fully molded, with gold plated contacts for a lifetime of use.

Features

- USB 2.0 Male-to-Female adapter, with Universal / Reversible Male connector
- Male end can be plugged in any direction
- USB2.0 Hi-Speed rated

Specifications

OVERVIEW	
Chromebook Compatible	Yes
Style	USB
Cable Types	USB
OUTPUT	
USB Charging	No
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Connector A	REVERSIBLE USB A (MALE)
Connector B	USB A (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.