

## Universal Reversible USB 2.0 Hi-Speed Cable, 28/24AWG (Reversible A to 5Pin Micro B M/M), 6-ft.

MODEL NUMBER: **UR050-006-24G**



### Description

Tripp Lite's UR050-006-24G 6-ft. USB 2.0 A to Micro-B cable features a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Micro-USB is the latest generation of USB connector, and is found on Cell Phones, PDA's, USB On-the-Go ( OTG ) devices, Digital Cameras, Tablets and more. Constructed of premium double-shielded cable with tinned copper braid and aluminum mylar foil featuring twisted 28AWG data lines and 24AWG power lines. 24AWG power lines allow for charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge. USB 2.0 rated cable handles 480Mbps data transfer rates.

### Features

- USB Universal / Reversible A Male to Micro-B Male
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

## Specifications

OVERVIEW	
Chromebook Compatible	Yes
Style	USB
Cable Types	USB
OUTPUT	

### Highlights

- Universal / Reversible "A" Male to Micro-B Male
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

### System Requirements

- Digital devices that use the USB Micro-B Female socket

### Package Includes

- 6-ft. USB2.0 Universal / Reversible A to Micro-USB B Device Cable, 28/24AWG (A Male to Micro-B Male)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

USB Charging	Yes
<b>INPUT</b>	
Cable Length (ft.)	6
Cable Length (m)	1.83
<b>PHYSICAL</b>	
Color	Black
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
<b>CONNECTIONS</b>	
Connector A	REVERSIBLE USB A (MALE)
Connector B	MICRO-USB B (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.