

Specifications

Technical (KD-DAXAA):

- » Input: PCM Coaxial Audio on (1) RCA Female, Digital Optical Audio on (1) Toslink connector
- » Output: Left and Right Analog Line Level Audio on (2) RCA Female
- » PCM Input: 1VPP/75Ω
- » Audio Format: 2CH PCM
- » Sampling Rate: 32 KHz, 44.1 KHz, 48 KHz, & 96 KHz

Technical (KD-AAXDA):

- » Input: Left and Right Analog Line Level Audio on (2) RCA Female
- » Output: PCM Coaxial Audio on (1) RCA Female, Digital Optical Audio on (1) Toslink connector
- » Audio Format: 2CH LPCM
- » Sampling Rate: 48 KHz

General:

- » Regulation: CE, FCC, RoHS, WEEE
- » Power: External 5V DC 2 Amp power supply
- » Dimensions: L=1.6" W=2" H=1"
- » Weight: 2.75 oz
- » Shipping Weight: 1 lb

