

RFM SERIES KITTED SEISMIC ZONE 4 SERVER CABINET



R. F. Mote Series Seismic Zone 4 Kitted Cabinets (30" and 24" Wide) are independently certified to meet UBC code seismic strength requirements for Zone 4 as per Bellcore GR-63-CORE specifications. Standard kitted Seismic cabinets include: 2 Perforated doors, 2 solid side panels, 2 pair cage-nut style mounting rails, levelling feet, cover plates, and hardware package.

In addition to standard configuration, Seismic zone 4 Cabinets support a wide variety of options such as: thermal management (fan assemblies, chimney ducts, air stops, brush kits), power bars, ground bars, cable troughs, vertical and horizontal cable mangers, shelves, perforated side panels, and door lock options. Optional accessories can be factory installed in configurations best suited to their end use, or ordered separately and installed by the customer.

Standard Features:

- Lockable perforated Front and Rear door (c/w multi-point latch system)
- Doors: Electronic and Combination lock options available
- 2 Solid, lockable, lift off side panels
- 2 Pair Mounting angles, punched to 19" EIA universal spacing for cage nuts
- 4 Grounding points
 - 2 in top (#10-32 x 1/2" stud)
 - 2 in base (1/4-20 x 1/2" stud)
- Top c/w cable access openings (cover plates provided)
- Hardware package (qty 24, 1/4-20 Cage nuts and screws)
- Adjustable levelling feet
- Durable textured powder coated finish
- Standard colour is all black
- Custom colours and sizes available upon request

Highlights:

- Heavy gauge steel
- All welded construction
- Provisions for fans and cable access
- Cabinet doors are field reversible; hinge kit required
- Seismic rated frame, Zone 4 Telcordia (Bellcore) GR-63-CORE

30" Wide Cabinet

	PART NUMBER	A	B	C	#of U's
19" MOUNT	RFM-304283-US-19S	30.150	42.150	83.00	44U
	RFM-303683-US-19S	30.150	36.150	83.00	44U
	RFM-303083-US-19S	30.150	30.150	83.00	44U

Note: 23" and 24" EIA mount also available for 30" wide cabinet

24" Wide Cabinet

	PART NUMBER	A	B	C	#of U's
19" MOUNT	RFM-244283-US-19S	24.00	42.150	83.00	44U
	RFM-243683-US-19S	24.00	36.150	83.00	44U
	RFM-243083-US-19S	24.00	36.150	83.00	44U

