



## Building Entrance Terminals

INDOOR - CABLE STUB TERMINATION SERIES - BET



### 1900-100K

100 PAIR - INDOOR BET - 25' OSP AIR CORE CABLE STUB/25' CABLE STUB -

### Product Specifications

#### UL 497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Loaded and Unloaded Models are "Buy America Act" Approved.

Circa's cable stub units offer the user a variety of installation and splicing options depending on application specific requirements. Custom cable stub lengths are available upon request. Standard stub length on the 1900 Series, stub to stub, is 25 feet. These units are also available with stubs in/out of equal length in 50 or 100 feet. The 1900A1-100K model can also be ordered with both stubs coming from the bottom or top. The units have an internal fuse link and use industry standard 5-pin protection modules.

## Features & Benefits

- 16AWG Powder Coated Steel Construction
- 26 AWG Input Cable Stub Serves as Fuse Link
- External Ground Connectors Accept 6 - 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- Equipped with Heavy Duty Strain Relief and Encapsulated Cable Connector



1900-100K

### Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
1900-100K	417018K25A25	100	Cable	Cable	10.00 x 10.75 x 4.50	24

Cable Type: 26AWG 25' OSP Rated Air Core Input 0.772 dia o.d. - 24AWG 25' Shielded CMR output 0.74 dia o.d.

Circa Telecom, Inc © 2013 - Version 1.03

6914 W. Linebaugh Ave - Tampa, FL 33625  
Phone 800.783.6556 - Fax 813.676.2060 - Email [circatech@circatelecom.com](mailto:circatech@circatelecom.com) - [www.circatelecom.com](http://www.circatelecom.com)



## Building Entrance Terminals

INDOOR - CABLE STUB TERMINATION SERIES - BET




### 1900-100K

100 PAIR - INDOOR BET - 25' OSP AIR CORE CABLE STUB/25' CABLE STUB -

### Physical Dimensions

UL 497 Primary Protector for Communication Circuits

10.00 x 10.75 x 4.50  
(H" x W" x D")



### Notes

Cable Type: 26AWG 25' OSP Rated Air Core Input 0.772 dia o.d. - 24AWG 25' Shielded CMR output 0.74 dia o.d.

Indoor Wall Mount

Custom cable lengths available in 25' increments

Previous Model Numbers: 2000-100, 1900-100