

**Interface and Converter Products****T&B Catalog Number:**

1SNA607204R1600

UPC Number:

66201927498

Status:

Active

Description:

R500, 5.08 mm wide, 24 VDC optocoupler module with screw clamp connections and a 100 milliamp rated solid state output

Features

Smallest spacing available - 5.08 mm

Application

For applications that require a 24 VDC output type optocoupler

General

Wire Size	24-12 AWG
Series	R500
Operation-Function	Optocoupler Module

Dimension Information

L x W x D (inches)	3.42 x 0.2 x 4.38
--------------------	-------------------

Specifications

Input Voltage (DC)	24
Rated Output Voltage (VDC)	4.5-58
Rated Output Current (Amps)	0.1

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	9 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com