Thomas&Betts



SNK Terminal Blocks T&B Catalog Number:

UPC Number:
Status:
Description:

1SNK506210R0000 80432548887 Active

Gray, double deck feed through terminal block with 6 mm spacing, 30 Amp rated UL current with screw clamp connection and 2 feed through circuits

	Easy and ergonomic mounting thanks to the unique
	profile
	Marking surfaces can be read clearly from any an- gle in an enclosure and are larger than standard markers
	One unique end section and circuit separator fits all feed-through terminal blocks, reducing the use of accessories
Application	
	For use with applications ranging from standard distribution and control panels, to specialized ap- plications in key industries such as traction, ener- gy, maritime, explosive atmospheres, material han- dling, etc.
General	
Style	Double Deck Feed Through
Color	Gray
Series	ZS6-D2
Connection Technology	Screw Clamp
Dimension Information	
Spacing (mm)	6
Spacing (inches)	0.236
Specifications	
UL Current (Amps)	30
UL Voltage (VAC)	300
IEC Voltage (VAC)	800
IEC Current (Amps)	41
Packaging	
T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	400
T&B Sold in UOM	Each
T&B Weight Per UOM	8.5 lbs. per 100

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@thb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com