



SNK Terminal Blocks

T&B Catalog Number:

1SNK506412R0000

UPC Number:

80432548902

Status:

Active

Description:

Gray and dark gray feed through terminal block for 5mm x 20mm fuses with blown fuse indicator by red 24-60 V red LED, with 6 mm spacing, 6.3 amp UL current with screw clamp connection

Features

Protect your circuits with 5x20 mm fuse terminal blocks compliant with IEC 60947-7-3 standard

Simplify the distribution thanks to the two jumper channels aligned with ZS4 feed-through and ZS4-S-R1 disconnect terminal blocks

Quickly identifies a defective circuit due to the blown fuse indicator (with leakage current < 0.5 mA).

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Fuse Holder
Color	Gray-Dark Gray
Mounting	DIN 3
Series	ZS4-SF-R1
Connection Technology	Screw Clamp
UL Wire Range (AWG)	24-10
Rated IEC Wire Range (Solid) (mm2)	0.2-4
Rated IEC Wire Range (Stranded) (mm2)	0.22-4

Dimension Information

L x W x H (mm)	70.3 x 6 x 78.8
Spacing (mm)	6
L x W x H (in)	2.77 x .236 x 3.10
Spacing (inches)	0.236

Specifications

UL Current (Amps)	6.3
UL Voltage (VAC)	150

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	400
T&B Sold in UOM	Each
T&B Weight Per UOM	0.04 lbs. Each

Certifications

Approvals	USR, CSA, CE
-----------	--------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com