

**Interface and Converter Products****T&B Catalog Number:**

1SVR011701R2500

**UPC Number:**

66201910186

**Status:**

Active

**Description:**

Temperature signal converter with 24 VDC supply voltage, and an output signal of 0-10 volts, 0-20 milliamps, 4-20 milliamps

**Features**

Plug and Work, no adjustment of single-function devices required

**Application**

For PT100 RTD input and voltage or milliamp output applications

**General**

Series

CC-E

Operation-Function

Signal Converter

**Approvals**

UL Class

Class 1, Div 2

**Dimension Information**

L x W x D (inches)

2.95 x 0.89 x 4.01

**Specifications**

Supply Voltage (DC)

24

Output Signal (mA)

0-20 or 4-20

Output Signal (V)

0-10

**Packaging**

Package in Units

1

T&amp;B Sold in UOM

Each

T&amp;B Weight Per UOM

25.5 lbs. per 100

**Certifications**

Approvals

UL1604

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com