

**Interface and Converter Products****T&B Catalog Number:**

1SVR011708R0400

UPC Number:

66201910238

Status:

Active

Description:

Measuring signal converter with 110-240 VAC supply voltage, an input signal of 0-5 amps or 0-20 amps, AC/DC and an output voltage of 0-10 volts, 0-20 milliamps or 4-20 milliamps

Features

Plug and Work, no adjustment required

3-way electrical isolation

Application

For 0-20 amps input and selectable voltage or milliamp output applications

General

Series CC-E

Operation-Function Signal Converter

Approvals

UL Class UL 508 Listed, UL 1604 Listed

Dimension Information

L x W x D (inches) 2.95 x 0.89 x 4.01

Specifications

Supply Voltage (AC) 110-240

Input Signal (A) 0-5 or 0-20

Output Signal (mA) 0-20 or 4-20

Output Signal (V) 0-10

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 26.5 lbs. per 100

Certifications

Approvals UL Listed, CSA

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com