

**Interface and Converter Products****T&B Catalog Number:**

1SVR011719R2600

UPC Number:

66201910175

Status:

Active

Description:

Standard signal converter with 24 VDC supply voltage, an input signal of -10...+10 V and an output signal of -10...+10 V

Features

Applied supply voltage is displayed by a green LED

Application

For minus 10 V to plus 10 V input and minus 10 V to plus 10 V output applications

General

Series	CC-E
Operation-Function	Signal Converter

Dimension Information

L x W x D (inches)	2.44 x 0.89 x 2.56
--------------------	--------------------

Specifications

Supply Voltage (DC)	24
Input Signal (V)	minus 10 to plus 10
Output Signal (V)	minus 10 to plus 10

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	0.21 lbs. Each

Certifications

Approvals	UL
-----------	----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com