

**Interface and Converter Products****T&B Catalog Number:**

1SVR011741R2400

**UPC Number:**

66201910221

**Status:**

Active

**Description:**

Temperature signal converter with 24 VDC supply voltage, an input signal of PT100 at minus 50 to 250 degrees celcius and an output signal of 4-20 milliamps

**Features**

Adjustment and operating elements on the front side

**Application**

For PT100 RTD at minus 50 to 100 degrees C input and 4-20 mA output applications

**General**

Series	CC-E
Operation-Function	Signal Converter

**Dimension Information**

L x W x D (inches)	2.44 x 0.89 x 2.56
--------------------	--------------------

**Specifications**

Supply Voltage (DC)	24
Sensor Input (Degrees C)	PT100 at minus 50 to 250
Output Signal (mA)	4-20

**Packaging**

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	20.5 lbs. per 100

**Certifications**

Approvals	UL
-----------	----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com