



Grommeting T&B Catalog Number:

UPC Number:

Status:

Description:

GRNY-052-0-C

72849410129

Active

Extruded Grommeting Black Nylon 6/6 For Max. Panel Thickness .052,
100 Feet Per Roll

Features

Used to line panel edges and knockouts where the chafing of wires is a concern.

Available in 8 stock sizes in 100-ft. lengths for panels from .040 - .250 inches thick and in a variety of stocked materials to cover a wide range of applications.

General

Style	Extruded
Material	Nylon 6/6
Color	Black

Dimension Information

For Panel Thickness Max (inches)	0.052
C (inches)	0.040
D (inches)	0.190
E (inches)	0.125

Specifications

Flammability Rating	UL 94 V-2
---------------------	-----------

Tooling

Application Tools	SR-100
-------------------	--------

Packaging

T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	20
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	0.95 lbs. Each

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com