



## Grommeting T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

GRNY-062-0-C  
72849407940  
Active

Extruded Grommeting Black Nylon 6/6 For Max. Panel Thickness .062,  
100 Feet Per Roll

### Features

Used to line panel edges and knockouts where the chafing of wires is a concern.

Available in 8 stock sizes in 100-ft. lengths for panels from .040 - .250 inches thick and in a variety of stocked materials to cover a wide range of applications.

### General

Style	Extruded
Material	Nylon 6/6
Color	Black

### Dimension Information

For Panel Thickness Max (inches)	0.062
C (inches)	0.045
D (inches)	0.200
E (inches)	0.170

### Specifications

Flammability Rating	UL 94 V-2
---------------------	-----------

### Tooling

Application Tools	SR-100
-------------------	--------

### Packaging

T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	15
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	1.25 lbs. Each

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com