## Thomas&Betts



## Grommeting T&B Catalog Number:

UPC Number: Status: Description: GRNY-085-0-C 72849409449 Active


Extruded Grommeting Black Nylon 6/6 For Max. Panel Thickness .085, 100 Feet Per Roll **Features** 

	Used to line panel edges and knockouts where the chafing of wires is a concern.
	Available in 8 stock sizes in 100-ft. lengths for pan- els from .040250 inches thick and in a variety of stocked materials to cover a wide range of applica- tions.
General	
Stude	Extruded
Style Material	
	Nylon 6/6
Color	Black
Dimension Information	
For Panel Thickness Max (inches)	0.085
C (inches)	0.045
D (inches)	0.200
E (inches)	0.170
Specifications	
Flammability Rating	UL 94 V-2
Tooling	
Application Tools	SR-100
Packaging	
T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	15
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	1 lbs. Each
Certifications	
RoHS Compliance	Yes
· .	

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com



Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com