



## Grommeting T&B Catalog Number:

**UPC Number:**

**Status:**

**Description:**

GRPE-125-9-C

72849408090

Active

Extruded Grommeting Natural Polyethylene For Max. Panel Thickness  
.125, 100 Feet Per Roll

### Features

Used to line panel edges and knockouts where the chafing of wires is a concern.

Available in 8 stock sizes in 100-ft. lengths for panels from .040 - .250 inches thick and in a variety of stocked materials to cover a wide range of applications.

### General

Style	Extruded
Material	Polyethylene
Color	Natural

### Dimension Information

For Panel Thickness Max (inches)	0.125
C (inches)	0.050
D (inches)	0.220
E (inches)	0.205

### Specifications

Flammability Rating	UL 94 HB
---------------------	----------

### Tooling

Application Tools	SR-100
-------------------	--------

### Packaging

T&B Order Multiple	1
T&B Inner Pack	1
Package in Units	10
Feet per Roll	100
T&B Sold in UOM	Each
T&B Weight Per UOM	1.36 lbs. Each

### Certifications

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com