



**Enclosed
T&B Catalog Number:**

T075LB4-48/XD

UPC Number:

80432519991

Status:

Active

Description:

Enclosed, extreme duty PST softstarter rated for 75 horsepower at 480V AC.

Features

- PST extreme duty provides reliable reduced voltage starting, and is our most advanced softstarter
- Short circuit protection
- Emergency start bypass
- Redundant electronic overload
- Built and tested to provide 500% rated current for 30 seconds
- UL508A label, UL service entrance rating
- A door mounted ABB hand-off-auto switch
- Three vibration resistant, LED type pilot lights
- Door interlocked disconnect handle that is padlockable and defeatable

Standards

UL508A, NEMA 4X

Application

- Extreme duty designed for high inertia load applications, such as rock crushers, mixers, hammer mills, and chippers
- By using closed loop current control in addition to voltage ramping the PST helps get every bit of performance from weak power systems

General

Series PST

Dimension Information

H x W x D (inches) 24 x 24 x 12

Specifications

Voltage 480V AC

Packaging

T&B Inner Pack 1
 Package in Units 1
 T&B Sold in UOM Each
 T&B Weight Per UOM 145 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com