

POWERED BY

SYSTIMAX®

760188417 | 360G2-iP-2U-288F-LC-DM-LS-UHD

SYSTIMAX 360™ iPatch® InstaPATCH 2U 288F-LC Distribution Module, LazrSPEED, UHD Shelf

Construction Materials

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber (OM2+) LazrSPEED® 300, 50 µm multimode fiber (OM3) LazrSPEED® 550, 50 µm multimode fiber (OM4)
Material Type	ABS Polycarbonate

Dimensions

Depth	492.76 mm 19.40 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	SYSTIMAX 360™ iPatch®
Intelligence Type	iPatch® enabled
Product Type	Shelf, preterminated
Rack Units	2
Shelf Movement	Fixed
Color	Black
Interface	LC
Package Quantity	1
Total Ports, quantity	144

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification