Thomas&Betts



UL 1077 **T&B Catalog Number:**

UPC Number:
Status:
Description:

S201-D10 66201916887 Active

1 pole, 10 amps rated at 480Y/277 VAC, UL 1077 series miniature circuit breaker with thermal-magnetic trip device, D trip curve, and 6kA interrupt current rating Features

	Mon and the second s
	High performance MCB provides compact supple-
	mentary, energy limiting, circuit protection
	Fast breaking time
	Bus connection system
	Finger safe terminals Suitable for reverse feed
Application	Suitable for reverse feed
Application	
	For use as a supplemental protection device
	Designed for use in cable protection applications,
	such as in control circuits and lighting applications
General	
Mounting Method	DIN Rail
Тгір Туре	Thermal-magnetic
Number of Poles	1
Series	S200-D
Terminal Type	Screw
Approvals	
UL Class	UL 1077
Dimension Information	
H x W x D (inches)	3.35 x 0.69 x 2.98
H x W x D (mm)	88 x 17.5 x 69
Specifications	
Rated Current (Amps)	10
Rated Voltage AC	480Y/277
Interrupt Rating (kA)	6
Trip Curve	D
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	0.28 lbs. Each

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com