



SNA Terminal Blocks

T&B Catalog Number:

UPC Number:

011527720

Status:

66201903353

Description:

Active

Yellow Plunger, heavy duty switch terminal block with 8 mm spacing, 40 Amp rated UL current with screw clamp connection that accepts 22 - 8 AWG UL wire range

Features

	Self-locking clamp design prevents screw loosening
	Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires
	Touch-safe IP20 protection
	High quality steel offers a very high over-torque resistance
	Compensates for the flattening of copper under contact pressure
	Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

	For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.
--	---

General

Style	Heavy Duty Switch
Color	Yellow
Mounting	DIN 1-3
Series	M 6/8.STP
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-8
Rated IEC Wire Range (Solid) (mm ²)	6
Rated CSA Wire Size (AWG)	8

Dimension Information

L x W x H (mm)	55.5 x 8 x 57.5
Spacing (mm)	8
L x W x H (in)	2.19 x .0315 x 2.27
Spacing (inches)	0.315

Specifications

UL Current (Amps)	40
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	8
IEC Voltage (VAC)	500
IEC Current (Amps)	15
CSA Voltage (VAC)	600
CSA Current (Amps)	15

Packaging

T&B Order Multiple	25
T&B Inner Pack	25
Package in Units	400

T&B Sold in UOM	Each
T&B Weight Per UOM	5 lbs. per 100

Certifications

Approvals	UL, IEC, CSA
-----------	--------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com