



Location: United States

T&B
529 Briggs Pl.

UL 1077

T&B Catalog Number:

S203-C10

UPC Number:

66201917688

Status:

Active

Description:

3 pole, 10 amps rated at 480Y/277 VAC, UL 1077 series miniature circuit breaker with thermal-magnetic trip device, C trip curve, and 6kA interrupt current rating

Features

- High performance MCB provides compact supplementary, energy limiting, circuit protection
- Fast breaking time
- Bus connection system
- Finger safe terminals
- Suitable for reverse feed

Application

- For use as a supplemental protection device
- Designed for use in cable protection applications, such as in control circuits and lighting applications
- For use with resistive loads

General

Mounting Method	DIN Rail
Trip Type	Thermal-magnetic
Number of Poles	3
Series	S200-C
Terminal Type	Screw

Approvals

UL Class	UL 1077
----------	---------

Dimension Information

H x W x D (inches)	3.35 x 2.07 x 2.98
H x W x D (mm)	88 x 52.5 x 69

Specifications

Rated Current (Amps)	10
Rated Voltage AC	480Y/277
Interrupt Rating (kA)	6
Trip Curve	C

Packaging

T&B Inner Pack	1
Package in Units	36
T&B Sold in UOM	Each
T&B Weight Per UOM	0.89 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com