



UL 1077

T&B Catalog Number:

S501-K20

UPC Number:

66201953648

Status:

Active

Description:

1 pole, 20 amps rated at 600Y/277 VAC, UL 1077 series miniature circuit breaker with adjustable trip device, K trip curve, and 30kA interrupt current rating

Features

High breaking capacity

Fast breaking time

Adjustable trip unit

Finger safe terminals

Multi-functional terminals

Application

For use as a supplemental protection device

Designed for the higher inrush currents during system start of inductive loads: as in motor and transformer applications

General

Mounting Method

DIN rail

Trip Type

Adjustable

Number of Poles

1

Series

S500-K

Terminal Type

Screw

Approvals

UL Class

UL 1077

Dimension Information

H x W x D (inches)

3.62 x .98 x 3.15

H x W x D (mm)

92 x 25 x 80

Specifications

Rated Current (Amps)

20

Rated Voltage AC

600Y/277

Interrupt Rating (kA)

30

Trip Curve

K

Packaging

Package in Units

1

T&B Sold in UOM

Each

T&B Weight Per UOM

0.51 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com