



Open
T&B Catalog Number:

PSE105-600-70

UPC Number:

80432557165

Status:

Active

Description:

Open PSE softstarter with maximum rated operational current of 104 amp for class 10 normal (N) starting applications and 80 amp for class 30 heavy duty (HD) starting applications, and 100 to 250V AC control voltage.

ABB Attributes

Class 10 (N) and 30 (HD)

Features

PSE is the efficient range of softstarter products in the ABB softstarter family

Torque control for excellent control of pumps

Built in bypass for saving energy and installation time

Built in electronic overload protection protects the motor from overheating

Analog output showing operational current

Coated circuit boards for reliable operation in harsh environments

Standards

UL, CSA

Application

Normal duty (N) starting applications such as pumps, compressors, elevators, escalators, short conveyor belts and bow thrusters.

Heavy duty (HD) starting applications, such as centrifugal fans, crushers, mixers, mills, stirrers and long conveyor belts

General

Series PSE

Dimension Information

H x W x D (inches) 9.65 x 3.15 x 7.30

Specifications

3dmodel Available on Website

Voltage 208 to 600V AC

Maximum rated operational current (A) 104 amp for class 10, and 80 amp for class 30

Control Voltage 100 to 250V AC

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 7.39 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

