



**Open
T&B Catalog Number:**

PSE300-600-70

UPC Number:

80432557170

Status:

Active

Description:

Open PSE softstarter with maximum rated operational current of 302 amp for class 10 normal (N) starting applications and 248 amp for class 30 heavy duty (HD) starting applications, and 100 to 250V AC control voltage.

ABB Attributes

Class	10 (N) and 30 (HD)
-------	--------------------

Features

	PSE is the efficient range of softstarter products in the ABB softstarter family
	Torque control for excellent control of pumps
	Built in bypass for saving energy and installation time
	Built in electronic overload protection protects the motor from overheating
	Analog output showing operational current
	Coated circuit boards for reliable operation in harsh environments

Standards

UL, CSA

Application

	Normal duty (N) starting applications such as pumps, compressors, elevators, escalators, short conveyor belts and bow thrusters.
	Heavy duty (HD) starting applications, such as centrifugal fans, crushers, mixers, mills, stirrers and long conveyor belts

General

Series	PSE
--------	-----

Dimension Information

H x W x D (inches)	21.65 x 6.44 x 9.31
--------------------	---------------------

Specifications

3dmodel	Available on Website
Voltage	208 to 600V AC
Maximum rated operational current (A)	302 amp for class 10, and 248 amp for class 30
Control Voltage	100 to 250V AC

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	33.38 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

