

**Molded Case Circuit Breakers****T&B Catalog Number:**

T6N600TW

**UPC Number:**

80432532961

**Status:**

Active

**Description:**

3 pole, 600 amps rated at 600V AC/DC, Tmax molded case circuit breaker with a thermal magnetic trip device and 35kA at 480V AC interrupt current rating

**Features**

Short circuit protection is provided by an adjustable magnetic trip unit

Advanced contact design and arcing chambers provide the latest in fault current protection

Adjustable trip point from 3000 to 6000A

Double insulation - allows UL Listed field installation of internal accessories

**Application**

For power distribution applications

Can be installed in either the horizontal or vertical planes

Suitable for reverse feed applications

**General**

Trip Type	Thermal Magnetic
Number of Poles	3
Series	T6

**Approvals**

UL Class	UL 489
----------	--------

**Dimension Information**

H x W x D (inches)	10.55 x 8.26 x 4.07
--------------------	---------------------

**Specifications**

Rated Current (Amps)	600
Rated Voltage AC	600
Rated Voltage DC	600
Interrupt Rating	35kA at 480V AC

**Packaging**

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	20.59 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com