



SNA Terminal Blocks T&B Catalog Number:

1SNA105143R2100

UPC Number:

80432540391

Status:

Active

Description:

Gray and orange heavy duty switch terminal block with blade, 6 mm spacing, 10 amp UL rated current, with double screw clamp

Features

Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Disconnect with Blade
Color	Gray and Orange
Mounting	DIN 1-3
Connection Technology	Screw Clamp

Dimension Information

Spacing (mm)	6
Spacing (inches)	0.238

Specifications

UL Current (Amps)	10
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	10
IEC Voltage (VAC)	320
IEC Current (Amps)	10

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	0.04 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com