



SNA Terminal Blocks

T&B Catalog Number:

016511510

UPC Number:

66201996022

Status:

Active

Description:

Green and yellow, ground block with 10 mm spacing and screw clamp connection that accepts 20-6 AWG UL wire range

Features

| | |
|--|--|
| | Self-locking clamp design prevents screw loosening |
| | Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires |
| | Touch-safe IP20 protection |
| | High quality steel offers a very high over-torque resistance |
| | Compensates for the flattening of copper under contact pressure |
| | Clamp is protected from harsh environments by a zinc bichromate surface treatment |

Application

| | |
|--|---|
| | For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc. |
|--|---|

General

| | |
|---|------------------|
| Style | Ground Block |
| Color | Green and Yellow |
| Mounting | DIN 1-3 |
| Series | M 10/10.P |
| Connection Technology | Screw Clamp |
| UL Wire Range (AWG) | 20-6 |
| Rated IEC Wire Range (Solid) (mm ²) | 10 |
| Rated CSA Wire Size (AWG) | 6 |

Dimension Information

| | |
|------------------|---------------------|
| L x W x H (mm) | 53 x 10 x 43.5 |
| Spacing (mm) | 10 |
| L x W x H (in) | 2.09 x 0.394 x 1.72 |
| Spacing (inches) | 0.394 |

Specifications

| | |
|--------------------------|---|
| Rated UL Wire Size (AWG) | 6 |
|--------------------------|---|

Packaging

| | |
|--------------------|----------------|
| T&B Order Multiple | 50 |
| T&B Inner Pack | 50 |
| Package in Units | 500 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.05 lbs. Each |

Certifications

| | |
|-----------|--------------|
| Approvals | UL, IEC, CSA |
|-----------|--------------|

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com