



## SNA Terminal Blocks

### T&B Catalog Number:

029968402

**UPC Number:**

66201997169

**Status:**

Active

**Description:**

Gray, feed through terminal block with 6 mm spacing, 20 Amp rated UL current with screw clamp connection that accepts 22-12 AWG UL wire range

### Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Triple Deck Feed Through
Color	Gray
Mounting	DIN 3
Series	M 4/6.T3.P
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-12
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	4
Rated CSA Wire Size (AWG)	12

### Dimension Information

L x W x H (mm)	90 x 6 x 72
Spacing (mm)	6
L x W x H (in)	3.54 x .238 x 2.83
Spacing (inches)	0.236

### Specifications

UL Current (Amps)	20
UL Voltage (VAC)	300
Rated UL Wire Size (AWG)	12
IEC Voltage (VAC)	500
IEC Current (Amps)	32
CSA Voltage (VAC)	300
CSA Current (Amps)	20

### Packaging

T&B Order Multiple	25
T&B Inner Pack	25
Package in Units	375

T&B Sold in UOM	Each
T&B Weight Per UOM	7.5 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)