

**UL 1077****T&B Catalog Number:**

S203-C6

UPC Number:

66201917736

Status:

Active

Description:

3 pole, 6 amps rated at 480Y/277 VAC, UL 1077 series miniature circuit breaker with thermal-magnetic trip device, C trip curve, and 6kA interrupt current rating

Features

High performance MCB provides compact supplementary, energy limiting, circuit protection

Fast breaking time

Bus connection system

Finger safe terminals

Suitable for reverse feed

Application

For use as a supplemental protection device

Designed for use in cable protection applications, such as in control circuits and lighting applications

For use with resistive loads

General

Mounting Method DIN Rail

Trip Type Thermal-magnetic

Number of Poles 3

Series S200-C

Terminal Type Screw

Approvals

UL Class UL 1077

Dimension Information

H x W x D (inches) 3.35 x 2.07 x 2.98

H x W x D (mm) 88 x 52.5 x 69

Specifications

Rated Current (Amps) 6

Rated Voltage AC 480Y/277

Interrupt Rating (kA) 6

Trip Curve C

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 0.92 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com