Thomas®Betts



UL 1077 T&B Catalog Number:

MCB 3P C 40A 480Y/277 SUPP

UPC Number: Status: Description: S203-C40 66201917731 Active

Features High performance MCB provides compact supplementary, energy limiting, circuit protection Fast breaking time Bus connection system Finger safe terminals Suitable for reverse feed Application For use as a supplemental protection device Designed for use with medium magnetic start up currents such as lighting and control panels For use with resistive loads General Mounting Method DIN Rail Trip Type Thermal-magnetic Number of Poles 3 Series S200-C Terminal Type Screw Approvals **UL** Class UL 1077 **Dimension Information** H x W x D (inches) 3.35 x 2.07 x 2.98 H x W x D (mm) 88 x 52.5 x 69 **Specifications** Rated Current (Amps) 40 480Y/277 Rated Voltage AC Interrupt Rating (kA) 6 Trip Curve С Packaging Package in Units 1 T&B Sold in UOM Each T&B Weight Per UOM 94 lbs. per 100

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com