

**UL 1077****T&B Catalog Number:**

S203-K50

**UPC Number:**

66201917173

**Status:**

Active

**Description:**

3 pole, 50 amps rated at 480Y/277 VAC, UL 1077 series miniature circuit breaker with thermal-magnetic trip device, K trip curve, and 6kA interrupt current rating

**Features**

High performance MCB provides compact supplementary, energy limiting, circuit protection

Fast breaking time

Bus connection system

Finger safe terminals

Suitable for reverse feed

**Application**

For use as a supplemental protection device

Designed for use in cable protection applications, such as in control circuits and lighting applications

**General**

Mounting Method	DIN Rail
Trip Type	Thermal-magnetic
Number of Poles	3
Series	S200-K
Terminal Type	Screw

**Approvals**

UL Class	UL 1077
----------	---------

**Dimension Information**

H x W x D (inches)	3.35 x 2.07 x 2.98
H x W x D (mm)	88 x 52.5 x 69

**Specifications**

Rated Current (Amps)	50
Rated Voltage AC	480Y/277
Interrupt Rating (kA)	6
Trip Curve	K

**Packaging**

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.01 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com