

Open T&B Catalog Number:

PSR16-600-70 66201926156

UPC Number: 66201 **Status:** Active

Description:

Open, compact range PSR softstarter with maximum rated operational current of 15.2 amps, and 100 to 240V AC control voltage.

Features	240 V AC control voltage.
i catules	
	Most compact softstarter ABB offers
	Flexible mounting: Din Rail or screw mount
	Easy set-up of three clearly marked potentiometers
	Built in by-pass for energy saving
	Run signal relay on all devices
	Sophisticated algorithm eliminating the DC-component and thereby providing excellent starting performance
	Can be easily connected to ABB manual motor starters via a special designed conection kit
	Optional fieldbus communication using Profibus, Modbus, Devicenet, or CANopen
Standards	
	UL, CSA
Application	OL, CSA
Application	
	Suitable for stopping pumps, designed to reduce water hammering and will allow a superior stop compared to the direct stop resulting from a star delta starter or a DOL starter.
General	
Series	PSR
Dimension Information	Total
H x W x D (inches)	5.51 x 1.77 x 4.49
Specifications	
3dmodel	Available on Website
Voltage	208 to 600V AC
Maximum rated operational current (A)	15.2
Control Voltage	100 to 240V AC
Packaging	
T&B Inner Pack	1
Package in Units	26
T&B Sold in UOM	Each
T&B Weight Per UOM	1.08 lbs. Each

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com