Thomas&Betts



Power Supplies T&B Catalog Number:

UPC Number: Status: Description: 1SVR427035R1000 80432545630 Active

Power supply with 90-132 VAC or 180-264 VAC or 210-375 VDC input voltage and 12 VDC at 10 amp rated output **Features**

	Power reserve up to 50%
Application	
	For applications that require cost effective 12 VDC at 10 amps power supply
General	
Series	CP-E
Operation-Function	Power Supply
Approvals	
UL Class	Class 1, Div 2
Dimension Information	
L x W x D (inches)	4.87 x 3.27 x 4.87
Specifications	
Input Voltage (AC)	90-132 or 180-264
Input Voltage (DC)	210-375
Rated Output Voltage (VDC)	12
Rated Output Current (Amps)	10
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	2.2 lbs. Each
Certifications	
Approvals	cULus Listed, CSA

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@thb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com