



SNA Terminal Blocks

T&B Catalog Number:

011512407

UPC Number:

66201902268

Status:

Active

Description:

Gray, feed through terminal block with 16 mm spacing, 150 Amp rated UL current with screw clamp connection that accepts 10-0 AWG UL wire range

Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Feed Through
Color	Gray
Mounting	DIN 1-3
Series	M 35/16
Connection Technology	Screw Clamp
UL Wire Range (AWG)	10-0
Rated IEC Wire Range (Solid) (mm ²)	35

Dimension Information

L x W x H (mm)	49 x 16 x 59
Spacing (mm)	16
L x W x H (in)	1.93 x 0.630 x 2.32
Spacing (inches)	0.63

Specifications

UL Current (Amps)	150
UL Voltage (VAC)	600
IEC Voltage (VAC)	800
IEC Current (Amps)	125
CSA Voltage (VAC)	600
CSA Current (Amps)	140

Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	300
T&B Sold in UOM	Each
T&B Weight Per UOM	11 lbs. per 100

Certifications

Approvals

UL, IEC, CSA

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com