



## UL 1077

### T&B Catalog Number:

S201-D25

### UPC Number:

66201916891

### Status:

Active

### Description:

1 pole, 25 amps rated at 480Y/277 VAC, UL 1077 series miniature circuit breaker with thermal-magnetic trip device, D trip curve, and 6kA interrupt current rating

### Features

High performance MCB provides compact supplementary, energy limiting, circuit protection

Fast breaking time

Bus connection system

Finger safe terminals

Suitable for reverse feed

### Application

For use as a supplemental protection device

Designed for use in cable protection applications, such as in control circuits and lighting applications

### General

Mounting Method

DIN Rail

Trip Type

Thermal-magnetic

Number of Poles

1

Series

S200-D

Terminal Type

Screw

### Approvals

UL Class

UL 1077

### Dimension Information

H x W x D (inches)

3.35 x 0.69 x 2.98

H x W x D (mm)

88 x 17.5 x 69

### Specifications

Rated Current (Amps)

25

Rated Voltage AC

480Y/277

Interrupt Rating (kA)

6

Trip Curve

D

### Packaging

T&B Inner Pack

1

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

0.3 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com