



## UL 489

**T&B Catalog Number:**

S802U-K30

**UPC Number:**

80432537217

**Status:**

Active

**Description:**

2 pole, 30 amps rated at 240 VAC, series miniature circuit breaker with thermal-magnetic trip device, K trip curve, and 50kA interrupt current rating

### Features

High performance MCB provides energy limiting circuit protection for branch circuit protection

Fast breaking time

Finger safe terminals

Multi-function terminals

Ring-tongue compatible

IEC current limiting

### Application

For use as branch protection

Designed for the higher inrush currents during system start of inductive loads: as in motor and transformer applications

### General

Mounting Method

DIN rail

Trip Type

Thermal-magnetic

Number of Poles

2

Series

S800U-K

Terminal Type

Screw

### Approvals

UL Class

UL 489

### Dimension Information

H x W x D (inches)

3.74 x 2.09 x 3.48

H x W x D (mm)

95 x 53 x 88.5

### Specifications

Rated Current (Amps)

30

Rated Voltage AC

240

Interrupt Rating (kA)

50

Trip Curve

K

### Packaging

Package in Units

1

T&B Sold in UOM

Each

T&B Weight Per UOM

1.1 lbs. Each

### Application Support

Product Brochure

Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321

