



UL 1077

T&B Catalog Number:

S201P-K8

UPC Number:

66201919573

Status:

Active

Description:

2 pole, 2 amp rated at 500 VDC, UL 1077 series miniature circuit breaker with thermal-magnetic trip device, K trip curve, and 10kA interrupt current rating

Features

High performance MCB provides compact supplementary, energy limiting, circuit protection

Fast breaking time

Bus connection system

Finger safe terminals

Suitable for reverse feed

Application

For use as a supplemental protection device

Designed for the higher inrush currents during system start of inductive loads: as in motor and transformer applications

For use with inductive loads

General

Mounting Method

DIN Rail

Trip Type

Thermal-magnetic

Number of Poles

1

Series

S200P-K

Terminal Type

Screw

Approvals

UL Class

UL 1077

Dimension Information

H x W x D (inches)

3.35 x 0.69 x 2.98

H x W x D (mm)

88 x 17.5 x 69

Specifications

Rated Current (Amps)

8

Rated Voltage AC

480Y/277

Interrupt Rating (kA)

10

Trip Curve

K

Packaging

T&B Inner Pack

1

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

30.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com