



**UL 1077**

**T&B Catalog Number:**

S201P-K32

**UPC Number:**

66201916917

**Status:**

Active

**Description:**

MCB 1P K 32A 480Y/277 SUPP

**Features**

High performance MCB provides compact supplementary, energy limiting, circuit protection

Fast breaking time

Bus connection system

Finger safe terminals

Suitable for reverse feed

**Application**

For use as a supplemental protection device

Designed for allowing higher in-rush currents during system startup such as motors and transformers

For use with inductive loads

**General**

Mounting Method: DIN Rail

Trip Type: Thermal-magnetic

Number of Poles: 1

Series: S200P-K

Terminal Type: Screw

**Approvals**

UL Class: UL 1077

**Dimension Information**

H x W x D (inches): 3.35 x 0.69 x 2.98

H x W x D (mm): 88 x 17.5 x 69

**Specifications**

Rated Current (Amps): 32

Rated Voltage AC: 480Y/277

Interrupt Rating (kA): 10

Trip Curve: K

**Packaging**

T&B Inner Pack: 1

Package in Units: 10

T&B Sold in UOM: Each

T&B Weight Per UOM: 31.94 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com