

Power Circuit Breakers**T&B Catalog Number:**

D3SC0FD00B000XC

UPC Number:

66201944629

Status:

Active

Description:

3 pole, 1600 amps rated at 600V, UL rated, with an interrupt rating of 65kA at 480V, and standard breaking capacity, Emax E2 air circuit breaker

Features

	Compact design
	Improved safety due to double insulation of live parts and total segregation between phases
	Same height and depth for both withdrawable and fixed versions

Application

	Circuit breaker for general protection such as plants, user complexes and electric lines
	Can be used to protect equipment feeder lines for electrical machines such as generators, motors, transformers or capacitors

General

Breaking Capacity	Standard
Closing Operation	Manual
Fixed/Drawout	Fixed
Frame Size	E3
Locking Provisions	Padlock provision (open)
Number of Poles	3
Series	D3
Contacts	10
Auxiliary Contacts	10

Specifications

Rated Current (Amps)	1600
Interrupt Rating	65kA at 480V AC

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	139 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com