



SNA Terminal Blocks

T&B Catalog Number:

035620021

UPC Number:

66201997718

Status:

Active

Description:

Gray, single pole distribution block with 35.2 mm spacing, 160 Amp rated UL current with screw clamp connection that accepts 8 to 00 AWG UL wire range

Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Distribution Block
Color	Gray
Mounting	DIN 3
Series	BRU
Connection Technology	Screw Clamp
UL Wire Range (AWG)	8-00
Rated IEC Wire Range (Solid) (mm ²)	70
Poles	1

Dimension Information

L x W x H (mm)	91 x 35.2 x 52.5
Spacing (mm)	35.2
L x W x H (in)	3.58 x 1.388 x 2.067
Spacing (inches)	1.386

Specifications

UL Current (Amps)	160
UL Voltage (VAC)	600
IEC Voltage (VAC)	600
IEC Current (Amps)	160
CSA Voltage (VAC)	600
CSA Current (Amps)	160

Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.53 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com