

**SNA Terminal Blocks**  
**T&B Catalog Number:**016580901  
66201996045  
Active**UPC Number:**  
**Status:**  
**Description:**

Green and yellow ground block with screw clamp connection, 6 mm spacing on a DIN 3 rail without screw

**Features**Top entry wire connection  
Touch-safe IP20 protection**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	D 2,5/5.P
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	0.2 - 4
Rated IEC Wire Range (Stranded) (mm <sup>2</sup> )	0.22 - 4

**Dimension Information**

L x W x H (mm)	43.5 x 6 x 48
Spacing (mm)	6
L x W x H (in)	1.72 x .238 x 1.89
Spacing (inches)	.238

**Specifications**

Rated UL Wire Size (AWG)	10
--------------------------	----

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	700
T&B Sold in UOM	Each
T&B Weight Per UOM	2.63 lbs. per 100

**For further technical assistance, please contact us...**Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)