



Open Switches
T&B Catalog Number:

UPC Number:
Status:
Description:

OT600U03
66201947563
Active

3 pole, 600 amps rated at 600 VAC, UL 98, open non-fusible disconnect switch

Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

Application

- Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.
- Motor feeder applications and motor feeder short circuit and ground fault protection
- Kits with base and/or DIN rail mounted switches and pistol handles
- null

General

Number of Poles: 3
Series: Non-fusible

Approvals

UL Class: UL 98

Dimension Information

H x W x D (inches): 12.07 x 10.48 x 5.43

Specifications

Rated Current (Amps): 600
Rated Voltage AC: 600

Packaging

Package in Units: 1
T&B Sold in UOM: Each
T&B Weight Per UOM: 14.66 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com