

**UL 489****T&B Catalog Number:**

SU203PR-K40

UPC Number:

80432563836

Status:

Active

Description:

3 pole, 40 amp rated at 480Y/277 VAC, UL 489 series miniature circuit breaker with thermal-magnetic trip device, K trip curve, and 10kA interrupt current rating

Features

UL current limiting
Fast breaking time
Bus connection system
Wide range of accessories
Suitable for reverse feed

Application

For use as branch protection
Designed for the higher inrush currents during system start of inductive loads: as in motor and transformer applications
For use with inductive loads

General

Mounting Method	DIN Rail
Trip Type	Thermal-magnetic
Number of Poles	3
Series	SU200PR-K
Terminal Type	Screw

Approvals

UL Class	UL 489
----------	--------

Dimension Information

H x W x D (inches)	4.53 x 2.07 x 2.72
H x W x D (mm)	115 x 52.5 x 69

Specifications

Rated Current (Amps)	40
Rated Voltage AC	480Y/277
Interrupt Rating (kA)	10
Trip Curve	K

Packaging

Package in Units	3
T&B Sold in UOM	Each
T&B Weight Per UOM	0.79 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com