

**Molded Case Circuit Breakers****T&B Catalog Number:**

T3NQ125TW

UPC Number:

66201919703

Status:

Active

Description:

3 pole, 125 amps rated at 480V AC and 500V DC, Tmax molded case circuit breaker, 100% rated with a thermal magnetic trip device and 25kA at 480V AC interrupt current rating

Features

Short circuit protection is provided by a precise magnetic coil

Advanced contact design and arcing chambers provide the latest in fault current protection

Double insulation - allows UL Listed field installation of internal accessories

Application

UL approved for 100% rated applications

For power distribution applications

Can be installed in either the horizontal or vertical planes

Suitable for reverse feed applications

General

Trip Type	Thermal Magnetic
Number of Poles	3
Series	T3

Approvals

UL Class	UL 489
----------	--------

Dimension Information

H x W x D (inches)	5.90 x 4.13 x 2.76
--------------------	--------------------

Specifications

Rated Current (Amps)	125
Rated Voltage AC	480
Rated Voltage DC	500
Interrupt Rating	25kA at 480V AC

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	3.85 lbs. Each

Certifications

File Nbr:

UL 489

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

