

**Molded Case Circuit Breakers****T&B Catalog Number:**

A1N020TW-1

**UPC Number:**

80432554216

**Status:**

Active

**Description:**

1 pole, 20 amps rated at 240V AC and 125V DC, fixed trip point molded case circuit breaker, with a thermal magnetic trip device and 14kA at 240V AC and 10kA at 125V DC interrupt current rating

**Features**

Smaller size with full protection

Fixed trip point

Front mounted terminals

**Application**

For panelboards with 15A - 100A capacity

Branch circuit protection where small low cost, fixed trip point breakers are required

**General**

Trip Type Thermal Magnetic

Number of Poles 1

Series A1N

**Approvals**

UL Class UL 489

**Dimension Information**

H x W x D (inches) 5.91 x 1.00 x 2.36

**Specifications**

Rated Current (Amps) 20

Rated Voltage AC 240

Rated Voltage DC 125

Interrupt Rating 14kA at 240V AC and 10kA at 125V DC

**Packaging**

Package in Units 1

T&amp;B Sold in UOM Each

T&amp;B Weight Per UOM 0.75 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com