

**Molded Case Circuit Breakers****T&B Catalog Number:**

TS3N060TW-2

UPC Number:

80432534701

Status:

Active

Description:

2 pole, 60 amps rated at 600V AC and 500V DC, Tmax molded case circuit breaker with a thermal magnetic trip device and 25kA at 480V AC interrupt current rating

Features

Short circuit protection is provided by a precise magnetic coil

Advanced contact design and arcing chambers provide the latest in fault current protection

Application

2 pole branch circuit protection

For power distribution applications

Can be installed in either the horizontal or vertical planes

Suitable for reverse feed applications

General

Trip Type	Thermal Magnetic
Number of Poles	2
Series	TS3

Approvals

UL Class	UL 489
----------	--------

Dimension Information

H x W x D (inches)	6.7 x 4.13 x 4.07
--------------------	-------------------

Specifications

Rated Current (Amps)	60
Rated Voltage AC	600
Rated Voltage DC	500
Interrupt Rating	25kA at 480V AC

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	5.85 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com