Thomas@Betts



Molded Case Circuit Breakers T&B Catalog Number:

A2N150TW

UPC Number: 80432557916 **Status:** Active

Status: Description:

3 pole, 150 amps rated at 240V AC and 250V DC, fixed trip point molded case circuit breaker, with a thermal magnetic trip device and 25kA at 240V AC/DC interrupt current rating

AC/DC interrupt current rating	
Features	
	Smaller size with full protection
	Fixed trip point
	Front mounted terminals
Application	
	For panelboards with 125A - 250A capacity
	Branch circuit protection where small low cost, fixed
	trip point breakers are required
General	
Trip Type	Thermal Magnetic
Number of Poles	3
Series	A2N
Approvals	
UL Class	UL 489
Dimension Information	
H x W x D (inches)	5.91 x 4.13 x 2.36
Specifications	
Rated Current (Amps)	150
Rated Voltage AC	240
Rated Voltage DC	250
Interrupt Rating	25kA at 240V AC/DC
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	3.16 lbs. Each

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com